



# Versamate Series 60A 3 Pole 4 Wire Plug Assembly - Reverse Service - AT Type

By Killark  
Catalog # [VP6034-S39](#)

60A 3 Pole 4 Wire Plug Assembly - Reverse Service - AT Type.



\*Representative Image

## Features

- Feature an octagonal body style, ensuring a sure grip when connecting or disconnecting.
- Insulators have high mechanical and dielectric strength.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Funneled conductor entry chambers lead all properly stripped conductors into terminals simultaneously.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Includes suitability for Type P marine cable.

## Application

Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as: Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Refineries, Chemical Plants, Grain Facilities, Textile Manufacturing, Food Processing Facilities

## General

Finish Type	Baked Powder Epoxy/Polyester Finish
Grommet Range	0.65-1.50
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style II
Type	<ul style="list-style-type: none"><li>• Pin &amp; Sleeve</li><li>• Pin &amp; Sleeve</li></ul>
UPC	783936078052

## Dimensions

Dimensions	8.81 in x 3.68 in x 3.68 in
Height	3.68 in
Length	8.81 in
Width	3.68 in

## Electrical Ratings

Amperage Rating	60 A
Frequency Rating	50-400 Hz
Voltage Rating	<ul style="list-style-type: none"><li>• 600 VAC</li><li>• 250 VDC</li></ul>

## Conductor Related

Number Of Wires	3
-----------------	---

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Versamate 60 Amp Allen Terminal IOM K1382](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-VP6034-S39-SPEC-EN | REV 1/2024