



Versamate Series 60A 3 Pole 4 Wire Plug Assembly - AT Type

By Killark
Catalog # [VP6034](#)

60A 3 Pole 4 Wire Plug Assembly - AT Type

Features

- Feature an octagonal body style, ensuring a sure grip when connecting or disconnecting.
- Insulators have high mechanical and dielectric strength.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Funneled conductor entry chambers lead all properly stripped conductors into terminals simultaneously.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Includes suitability for Type P marine cable.

General

Catalog Number	VP6034
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder
	Epoxy/Polyester Finish
Grommet Range	0.65-1.50
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style II
UPC	783936078038

Dimensions



Dimensions	8.81 in x 3.68 in x 3.68 in
Height	3.68 in
Length	8.81 in
Weight	3.39 lb
Width	3.68 in

Electrical Ratings

Amperage Rating	60 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	3
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - VP6034 / VP6485 Engineering Drawing](#)
- [Installation Manuals - Versamate 60 Amp Allen Terminal IOM K1382](#)
- [Sales Drawings - VP6034 / VP6485 Sales Drawing](#)
- [Specifications - Versamate 60 AMP Replacement Parts Allen Terminal](#)
- [Specifications - VP6034 Specification Sheet French](#)
- [Specifications - VP6034 Specification Sheet English](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)



A Hubbell brand