



Versamate Series 60A 3 Pole 3 Wire Plug Assembly - Reverse Service

By Killark
Catalog # [VP6375-S39](#)

60A 3 Pole 3 Wire Plug Assembly - Reverse Service

Features

-
-
-
-
-
-

General

Catalog Number	VP6375-S39
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder Epoxy/Polyester Finish
Grommet Range	0.65-1.50
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style I
UPC	783936398549

Dimensions

Dimensions	8.81 in x 3.68 in x 3.68 in
Height	3.68 in



Length	8.81 in
Width	3.68 in

Electrical Ratings

Amperage Rating	60 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	3
-----------------	---

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 60 Amp Original Terminal IOM K1191](#)
- [Specifications - Versamate 60 AMP Replacement Parts Original Terminal](#)
- [Specifications - VP6375-S39 Specification Sheet French](#)
- [Specifications - VP6375S39 Specification Sheet English](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)



A Hubbell brand