



Versamate Series 60A 4 Pole 4 Wire Plug Assembly

By Killark
Catalog # [VP6475](#)

60A 4 Pole 4 Wire Plug Assembly



Features

- Feature an octagonal body style, ensuring a sure grip when connecting or disconnecting.
- Insulators have high mechanical and dielectric strength.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Funneled conductor entry chambers lead all properly stripped conductors into terminals simultaneously.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Includes suitability for Type P marine cable.

Application

Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Refineries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities

Specifications

EU RoHS Indicator Contact Manufacturer

Conductor

Number Of Wires 4

Current

| | |
|------------------|--|
| Amperage Rating | 60 A |
| Frequency Rating | 50-400 Hz |
| Voltage Rating | <ul style="list-style-type: none"> • 600 VAC • 250 VDC |

Dimensions

| | |
|---------------|-----------------------------|
| Width | 3.68 in |
| Height | 3.68 in |
| Grommet Range | 0.65-1.50 |
| Length | 8.81 in |
| Dimensions | 8.81 in x 3.68 in x 3.68 in |

General

| | |
|-------------|--|
| Type | Pin & Sleeve |
| Series | VersaMate Series |
| Material | <ul style="list-style-type: none"> • Body-Copper-free aluminum • Contacts-Brass • Spring tensioner-Patented beryllium copper • External screws-316 stainless steel |
| Finish Type | Baked Powder Epoxy/Polyester Finish |
| UPC | 783936834511 |
| Style | Style I |

Product Assets

[Installation Manual \[English\]](#)