



By Killark
Catalog # [VPR3044](#)

30A 4W4P Connector Assembly With Allen Terminals



Features

- Feature an octagonal body style, ensuring a sure grip when connecting or disconnecting.
- Insulators have high mechanical and dielectric strength.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Funneled conductor entry chambers lead all properly stripped conductors into terminals simultaneously.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Includes suitability for Type P marine cable.

Application

Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Refineries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities

Specifications

EU RoHS Indicator Contact Manufacturer

Conductor

Number Of Wires 4

Current

Amperage Rating 30 A
Frequency Rating 50-400 Hz
Voltage Rating 600 VAC;250 VDC

Dimensions

Width 3.06 in
Weight 1.98 lb.
Height 3.06 in
Grommet Range 0.55-1.20
Length 7.53 in
Dimensions 7.53 in x 3.06 in x 3.06 in

General

Type Pin & Sleeve
Series VersaMate
Material Body-Copper-free aluminum;
Contacts-Brass; Spring
tensioner-Patented beryllium
copper; External screws-316
stainless steel
UPC 783936078311
Style Style I

Product Assets

[Installation Manual \[English\]](#)