



VQ1F26S30 - VQ1F Series - Aluminum 26 Watt Compact Fluorescent Light Fixture (Lamp Included) - 120-277V At 50/60 Hz - Optic Thread Size 5-1/2 Inch

By Killark
Catalog # [VQ1F26S30](#)



VQ1F Series - Aluminum 26 Watt Compact Fluorescent Light Fixture (Lamp Included) - 120-277V At 50/60 Hz - Optic Thread Size 5-1/2 Inch.

Features

- World Voltage Ballast 120 through 277 VAC 50/60Hz
- Six mounting splice box types: Pendant, Ceiling, Wall bracket, Cone Top, 25° Angle Stanchion, Straight Stanchion - in a variety of entry sizes, including M20 for the VMX ceiling style.
- Elevated ambients to 55°C 13W - 64W
- Two lamp models have 2 ballasts for separate switching or system redundancy
- Normally shipped as components for fast delivery, or may be ordered factory assembled.
- Options for Fuses and Quick Disconnect
- Tank assemblies include quad-pin lamp

General

Catalog Number	VQ1F26S30
Color	Tan bronzor
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Quad Pin
Light Source	
Lumen Range	0-2,000 lm
Lumens	1800
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Luminaire Only
Series	VQ1F
Type	
UPC	783936076720

Dimensions

Dimensions	14.06 in x 6 in x 14.06 in
Gross Weight with Packaging	12.5
Height	14.06 in
Length	14.06 in
Width	6 in

Electrical Ratings

Frequency Rating	50/60 Hz
Lumens Per Watt	69.2
Voltage Rating	120-277 VAC
Wattage	26 W

Certifications And Compliance

Hazardous Rating(s)	Class I, Division 2, Groups A, B, C, D Class I, Zone 2, Groups IIC, IIB, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
---------------------	--

Product Assets

- [Certifications - VQ1F/VQ2F Series CSA Cert](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_VQ1F, VQ2F Series Luminaires IOM_K1361](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-VQ1F26S30-SPEC-EN | REV 6/2024