



VQ2F3630 - VQ2F Series, AL 36
Watt Compact Fluorescent Light
Fixture (Two 18W Lamps Included),
120-277V, 50/60 Hz, Optic Thread
Size 7-3/4"

By Killark
Catalog # [VQ2F3630](#)

VQ2F Series - Aluminum 36 Watt Compact Fluorescent Light
Fixture (Two 18W Lamps Included) - 120-277V At 50/60 Hz -
Optic Thread Size 7-3/4Inch

Features

-
-
-
-
-
-
-

General

Catalog Number	VQ2F3630
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Quad Pin
Light Source	Compact Fluorescent
Lumen Range	2,001-5,000 lm
Lumens	2400
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Luminaire Only
Optic Type	Luminaire Only
Series	VQ2F
Type	Aluminum Compact Fluorescent Fixture
UPC	783936076867

Dimensions

Dimensions	14.06 in x 6 in x 14.06 in
------------	----------------------------



Gross Weight with Packaging	11.5
Height	14.06 in
Length	14.06 in
Width	6 in

Electrical Ratings

Frequency Rating	50/60 Hz
Lumens Per Watt	66.7
Voltage Rating	120-277 VAC
Wattage	36 W

Certifications And Compliance

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	---

Product Assets

- [Certifications - VQ1F/VQ2F Series CSA Cert](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_VQ1F, VQ2F Series Luminaires IOM_K1361](#)
- [Specifications - VQ2F3630 Specification Sheet French](#)
- [Specifications - VQ2F3630 Specification Sheet English](#)
- [Specifications - VQ1F/VQ2F Series Compact Fluorescent Fixtures Specification Sheet](#)