



VQ2F5219 - VQ2F Series - Aluminum 52 Watt Compact Fluorescent Light Fixture (Two 26W Lamps Included) - 120VDC - Optic Thread Size 7-3/4Inch

By Killark
Catalog # [VQ2F5219](#)

VQ2F Series - Aluminum 52 Watt Compact Fluorescent Light Fixture (Two 26W Lamps Included) - 120VDC - Optic Thread Size 7-3/4Inch

Features

-
-
-
-
-
-
-

General

Catalog Number	VQ2F5219
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Quad Pin
Light Source	Compact Fluorescent
Lumen Range	2,001-5,000 lm
Lumens	3600
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Luminaire Only
Optic Type	Luminaire Only
Series	VQ2F
UPC	783936095370

Electrical Ratings

Lumens Per Watt	69.2
Voltage Rating	120 VDC
Wattage	52 W

Certifications And Compliance

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	---

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Certifications - VQ1F/VQ2F Series CSA Cert](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_VQ1F, VQ2F Series Luminaires IOM_K1361](#)
- [Specifications - VQ2F5219 Specification Sheet French](#)
- [Specifications - VQ2F5219 Specification Sheet English](#)
- [Specifications - VQ1F/VQ2F Series Compact Fluorescent Fixtures Specification Sheet](#)

