



Versamate Series 100A 4 Pole 4 Wire Receptacle - E Type Box - 1-1/2"

By Killark
Catalog # [VR1041E5](#)



VERSA REC STYLE I 100A 4W4P ETYPE 1-1/2"

Features

-
-
-
-
-

General

Back Box Type	DEAD END
Catalog Number	VR1041E5
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder
	Epoxy/Polyester Finish
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Number Of Poles	4
Series	VersaMate
Style	Style I

UPC783936835051

Dimensions

Hub Size1-1/2"

Electrical Ratings

Amperage Rating	100 A
Frequency Rating	50-400 Hz
Voltage Rating	• 621 VAC • 250 VDC

Conductor Related

Number Of Wires4

Product Assets

- [Installation Manuals - Versamate 100 Amp Original Terminal IOM K1192](#)
- [Specifications - VR1041E5 Specification Sheet English](#)
- [Specifications - VR1041E5](#)
- [Specifications - Versamate 100 AMP Replacement Parts Original Terminal](#)