




# Versamate Series 100A 3 Pole 4 Wire Receptacle Assembly - Reverse Service

By Killark  
Catalog # [VR1042-S39](#)

100A 3 Pole 4 Wire Receptacle Assembly - Reverse Service.



## Features

- Patented “Breech-Lock” cap serves as both flip lid and screw cover.
- Patented notch in cap arm holds cap open for easy plug insertion or maintenance.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Patented pin design uses slotted spring clip which avoids excessive wear while providing continuous electrical pin to sleeve contact.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Boxes come with a green grounding screw.

## Application

Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as: Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Refineries, Chemical Plants, Grain Facilities, Textile Manufacturing, Food Processing Facilities

## General

Finish Type	Finition époxy/polyester en poudre cuite
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style II
Type	<ul style="list-style-type: none"><li>• Pin &amp; Sleeve</li><li>• Pin &amp; Sleeve</li></ul>
UPC	783936376103

## Dimensions

Dimensions	5.37 in x 4.25 in x 4.75 in
Height	4.75 in
Length	5.37 in
Width	4.25 in

## Electrical Ratings

Amperage Rating	100 A
Frequency Rating	50-400 Hz
Voltage Rating	<ul style="list-style-type: none"><li>• 600 VAC</li><li>• 250 VDC</li></ul>

## Conductor Related

Number Of Wires	3
-----------------	---

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Versamate 100 Amp Original Terminal IOM K1192](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-VR1042-S39-SPEC-EN | REV 1/2024