



# Versamate Series 200A 2 Pole 3 Wire Receptacle with E Type Box 1-1/2"

By Killark  
Catalog # [VR20322E5](#)

200A 2 Pole 3 Wire Receptacle with E Type Box 1-1/2".



\*Representative Image

## Features

Boxes come with a green grounding screw.

## General

|                   |  |
|-------------------|--|
| Back Box Type     | DEAD END   |
| EU RoHS Indicator | Contact Manufacturer   |
| Finish Type       | Finition époxy/polyester en poudre cuite   |
| Material          | Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel |
| Series            | VersaMate  |
| Style             | Style II   |
| Type              |  |
| UPC               | 783936833194   |

## Dimensions

|            |                              |
|------------|------------------------------|
| Dimensions | 9.87 in x 8.19 in x 10.81 in |
| Height     | 10.81 in                     |
| Hub Size   | 1-1/2"                       |
| Length     | 9.87 in                      |
| Width      | 8.19 in                      |

## Electrical Ratings

|                  |   |
|------------------|---|
| Amperage Rating  | 200 A   |
| Frequency Rating | 50-400 Hz   |
| Voltage Rating   | <ul style="list-style-type: none"><li>• 600 VAC</li><li>• 250 VDC</li></ul> |

## Conductor Related

|                 |   |
|-----------------|---|
| Number Of Wires | 2 |
|-----------------|---|

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

## Product Assets

[Certifications - Versamate Series UL Certification](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Versamate 200 Amp IOM K1206](#)



A proud member of the Hubbell Family.