



Versamate Series 200A 2 Pole 3 Wire Receptacle with E Type Box 2" - Reverse Service

By Killark
Catalog # [VR20322E6-S39](#)

200A 2 Pole 3 Wire Receptacle with E Type Box 2" - Reverse Service

Features

- Patented “Breech-Lock” cap serves as both flip lid and screw cover.
- Patented notch in cap arm holds cap open for easy plug insertion or maintenance.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Patented pin design uses slotted spring clip which avoids excessive wear while providing continuous electrical pin to sleeve contact.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Boxes come with a green grounding screw.

General

Back Box Type	DEAD END
Catalog Number	VR20322E6-S39
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder
	Epoxy/Polyester Finish
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style II
UPC	783936063706

Dimensions



*Representative Image

Dimensions	9.87 in x 8.19 in x 10.81 in
Height	10.81 in
Hub Size	2"
Length	9.87 in
Width	8.19 in

Electrical Ratings

Amperage Rating	200 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	2
-----------------	---

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Certifications - Versamate Series UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 200 Amp IOM K1206](#)
- [Specifications - VR20322E6-S39](#)
- [Specifications - VR20322E6S39 Specification Sheet English](#)
- [Specifications - Versamate 200 AMP Replacement Parts Reverse Service](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)