



Versamate Series 200A 4 Pole 4 Wire Receptacle Assembly

By Killark
Catalog # [VR20412](#)

200A 4 Pole 4 Wire Receptacle Assembly

Features

-
-
-
-
-
-

General

Catalog Number	VR20412
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder
	Epoxy/Polyester Finish
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style I
UPC	783936833132

Dimensions



Dimensions	7.87 in x 6.83 in x 7.59 in
Height	7.59 in
Length	7.87 in
Width	6.83 in

Electrical Ratings

Amperage Rating	200 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	4
-----------------	---

Product Assets

- [Certifications - Versamate Series UL Certification](#)
- [Certifications - CSA Certificate - 200 Amp Versamate Series](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 200 Amp IOM K1206](#)
- [Specifications - Versamate 200 AMP Replacement Parts](#)
- [Specifications - VR20412 Specification Sheet English](#)
- [Specifications - VR20412](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)