



Versamate Series 30A 3 Pole 4 Wire Receptacle - AT Type

By Killark
Catalog # [VR3034](#)

30A 3 Pole 4 Wire Receptacle - AT Type

Features

-
-
-
-
-
-

General

Catalog Number	VR3034
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder
	Epoxy/Polyester Finish
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style II
UPC	783936078823

Dimensions

Dimensions	3.25 in x 3.41 in x 3.89 in
------------	-----------------------------



Height	3.89 in
Length	3.25 in
Weight	1.48 lb
Width	3.41 in

Electrical Ratings

Amperage Rating	30 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	3
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 30 Amp Allen Terminal IOM K1381](#)
- [Specifications - VR3034 Specification Sheet French](#)
- [Specifications - VR3034 Specification Sheet English](#)
- [Specifications - Versamate 30 AMP Replacement Parts Allen Terminal](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)