



Versamate Series 30A 4 Pole 4 Wire Receptacle - AT Type - 3/4" D Type Box - Polarized

By Killark
Catalog # [VR3044D2-S37](#)

30A 4 Pole 4 Wire Receptacle - AT Type - 3/4" D Type Box - Polarized

Features

- Patented “Breech-Lock” cap serves as both flip lid and screw cover.
- Patented notch in cap arm holds cap open for easy plug insertion or maintenance.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Patented pin design uses slotted spring clip which avoids excessive wear while providing continuous electrical pin to sleeve contact.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Boxes come with a green grounding screw.

General

Back Box Type	ANGLED FEED THRU
Catalog Number	VR3044D2-S37
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder
	Epoxy/Polyester Finish
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style I
UPC	783936088617

Dimensions



Dimensions	5.56 in x 4.25 in x 4.25 in
Height	4.25 in
Hub Size	3/4"
Length	5.56 in
Width	4.25 in

Electrical Ratings

Amperage Rating	30 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	4
-----------------	---

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 30 Amp Allen Terminal IOM K1381](#)
- [Specifications - Versamate 30 AMP Replacement Parts Allen Terminal](#)
- [Specifications - VR3044D2-S37](#)
- [Specifications - VR3044D2S37 Specification Sheet English](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)