



Versamate Series 60A 2 Pole 3 Wire Receptacle with D Type Box 1-1/2" - Polarized

By Killark
Catalog # [VR632D5-S37](#)

60A 2 Pole 3 Wire Receptacle with D Type Box 1-1/2" - Polarized

Features

- Patented “Breech-Lock” cap serves as both flip lid and screw cover.
- Patented notch in cap arm holds cap open for easy plug insertion or maintenance.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Patented pin design uses slotted spring clip which avoids excessive wear while providing continuous electrical pin to sleeve contact.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Boxes come with a green grounding screw.

General

Back Box Type	ANGLED FEED THRU
Catalog Number	VR632D5-S37
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder
	Epoxy/Polyester Finish
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style II
UPC	783936065229



Dimensions

Dimensions	7.5 in x 5.15 in x 5.75 in
Height	5.75 in
Hub Size	1-1/2"
Length	7.5 in
Width	5.15 in

Electrical Ratings

Amperage Rating	60 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	2
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 60 Amp Original Terminal IOM K1191](#)
- [Specifications - Versamate 60 AMP Replacement Parts Original Terminal](#)
- [Specifications - VR632D5S37 Specification Sheet English](#)
- [Specifications - VR632D5-S37](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)