



Versamate Series 60A 3 Pole 4 Wire Receptacle Assembly

By Killark
Catalog # [VR642](#)

60A 3 Pole 4 Wire Receptacle Assembly

Features

-
-
-
-
-
-

General

Catalog Number	VR642
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder
	Epoxy/Polyester Finish
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel
Series	VersaMate
Style	Style II
UPC	783936834504

Dimensions



Dimensions	4.5 in x 4.25 in x 4.66 in
Height	4.66 in
Length	4.5 in
Width	4.25 in

Electrical Ratings

Amperage Rating	60 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	3
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Versamate 60 Amp Original Terminal IOM K1191](#)
- [Specifications - VR642 Specification Sheet English](#)
- [Specifications - VR642](#)
- [Specifications - Versamate 60 AMP Replacement Parts Original Terminal](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)