



# Versamate Series 150A 3 Pole 4 Wire Receptacle Assembly

By Killark  
Catalog # [VRA15034](#)

150A 3 Pole 4 Wire Receptacle Assembly

## Features

- Patented “Breech-Lock” cap serves as both flip lid and screw cover.
- Patented notch in cap arm holds cap open for easy plug insertion or maintenance.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Patented pin design uses slotted spring clip which avoids excessive wear while providing continuous electrical pin to sleeve contact.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Boxes come with a green grounding screw.

## General

|                   |                                                                                                                            |
|-------------------|----------------------------------------------------------------------------------------------------------------------------|
| Catalog Number    | VRA15034                                                                                                                   |
| EU RoHS Indicator | Contact Manufacturer                                                                                                       |
| Finish Type       | Baked Powder                                                                                                               |
|                   | Epoxy/Polyester Finish                                                                                                     |
| Material          | Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium copper; External screws-316 stainless steel |
| Series            | VersaMate                                                                                                                  |
| Style             | Style II                                                                                                                   |



UPC 783936084046

## Dimensions

|            |                             |
|------------|-----------------------------|
| Dimensions | 5.37 in x 4.25 in x 4.75 in |
| Height     | 4.75 in                     |
| Length     | 5.37 in                     |
| Weight     | 4 lb                        |
| Width      | 4.25 in                     |

## Electrical Ratings

|                  |                                                                             |
|------------------|-----------------------------------------------------------------------------|
| Amperage Rating  | 150 A                                                                       |
| Frequency Rating | 50-400 Hz                                                                   |
| Voltage Rating   | <ul style="list-style-type: none"><li>• 600 VAC</li><li>• 250 VDC</li></ul> |

## Conductor Related

|                 |   |
|-----------------|---|
| Number Of Wires | 3 |
|-----------------|---|

## Product Assets

- [Certifications - VRA Series 150A Versamate UL Certification](#)
- [Certifications - CSA Certificate - 150 Amp Versamate](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - VRA15034](#)
- [Specifications - VRA15034 Specification Sheet English](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)



A Hubbell brand