



WLALFP1630L5D - 16k Lumen - Standard Location Linear Food Processing Light - 120-277VAC - 5 ft

By Killark
Catalog # [WLALFP1630L5D](#)



16k Lumen - Standard Location Linear Food Processing Light - 120-277VAC - 5 ft

General

Catalog Number	WLALFP1630L5D
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Light Source	LED
Lumen Range	15,001-25,000 lm
Lumens	15090
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	- Pendant - Surface
Optic Type	Polycarbonate Lens - Diffused
Series	WLALFP
UPC	783936153216

Dimensions

Weight	36.5 lb
--------	---------

Electrical Ratings

Frequency Rating	50/60 Hz
Lumens Per Watt	125.8
Voltage Rating	120-277 VAC
Wattage	120 W

Certifications And Compliance

IP Rating	- IP66 - IP67
-----------	---

Product Assets

- [Certifications - LALFP, WLALFP, & LZ2NL NSF Certificate](#)
- [Certifications - LAL Series CSA Certificate Of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - WLAL Series LED Luminaries IOM K1486](#)
- [Specifications - WLALFP1630L5D Specification Sheet French](#)
- [Specifications - LALFP Series Food Processing Light Specification Sheet](#)
- [Specifications - WLALFP1630L5D Specification Sheet English](#)