



WLALFP230L1D - 2k Lumen- Standard Location Food Processing Light - 120-277VAC - 1 ft

By Killark
Catalog # [WLALFP230L1D](#)



2k Lumen- Standard Location Food Processing Light - 120-277VAC - 1 ft

General

Catalog Number	WLALFP230L1D
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Light Source	LED
Lumen Range	0-2,000 lm
Lumens	1503
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	• Pendant • Surface
Optic Type	Polycarbonate Lens - Diffused
Series	WLALFP
UPC	783936153094

Electrical Ratings

Frequency Rating	50/60 Hz
------------------	----------

Lumens Per Watt	100.2
Voltage Rating	120-277 VAC
Wattage	15 W

Certifications And Compliance

IP Rating	• IP66 • IP67
-----------	---

Product Assets

- [Certifications - LALFP, WLALFP, & LZ2NL NSF Certificate](#)
- [Certifications - LAL Series CSA Certificate Of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - WLAL Series LED Luminaries IOM K1486](#)
- [Specifications - WLALFP230L1D Specification Sheet English](#)
- [Specifications - WLALFP230L1D Specification Sheet French](#)
- [Specifications - LALFP Series Food Processing Light Specification Sheet](#)