



WLALFP430L1D - 4k Lumen - Standard Location Food Processing Light - 120-277VAC - 1 ft

By Killark
Catalog # [WLALFP430L1D](#)



4k Lumen - Standard Location Food Processing Light - 120-277VAC - 1 ft

General

Catalog Number	WLALFP430L1D
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Light Source	LED
Lumen Range	2,001-5,000 lm
Lumens	3261
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	- Pendant - Surface
Optic Type	Polycarbonate Lens - Diffused
Series	WLALFP
UPC	783936153124

Dimensions

Weight	12.03 lb
--------	----------

Electrical Ratings

Frequency Rating	50/60 Hz
Lumens Per Watt	93.2
Voltage Rating	120-277 VAC
Wattage	35 W

Certifications And Compliance

IP Rating	- IP66 - IP67
-----------	---

Product Assets

- [Certifications - LALFP, WLALFP, & LZ2NL NSF Certificate](#)
- [Certifications - LAL Series CSA Certificate Of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - WLAL Series LED Luminaries IOM K1486](#)
- [Specifications - LALFP Series Food Processing Light Specification Sheet](#)
- [Specifications - WLALFP430L1D Specification Sheet English](#)
- [Specifications - WLALFP430L1D Specification Sheet French](#)