



WML-X Series LED Area light 250 Watt, 120-277VAC, 28000 Lumen 1-1/4" 25° Stanchion Mount

By Killark
Catalog # [WML3X2830D4G](#)



The WML-X area lowbay/highbay light fixture is suitable for harsh and heavy wet location rated environments. The WML-X is designed with improved LED's and pre-installed optics to direct the light where it is needed for various applications. The fixture tank and mounts are made with a cast copper-free aluminum housing and an internal heat sinking driver plate. Easily upgrade outdated HID lighting and help keep facilities operating safely and productively.

General

Catalog Number	WML3X2830D4G
Color Temperature	5000 K
Environmental Conditions	<ul style="list-style-type: none">• Suitablefor Wet Locations• Type 3, 4X• IP66• Marine Rated (US Only)
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	23,000 - 28,000 lm
Lumens	28000
Mounting Type	25° Stanchion
Optic Type	Glass Globe
Series	WML-X

Dimensions

Hub Size	1-1/4"
----------	--------

Electrical Ratings

Current / Amperage Rating	2.08-0.09 A
Frequency Rating	50-60 Hz
Voltage Rating	120-277 VAC
Wattage	250 W

Product Assets

- [Brochures - VMLX-WMLX Brochure - CA - English](#)
- [Brochures - VMLX-WMLX Brochure - CA - French](#)
- [Brochures - VML-X_Series-WML-X_Series](#)
- [Catalog Page - VMLX-WMLX Catalogue - CA - French](#)
- [Catalog Page - VMLX-WMLX Catalogue - CA - English](#)
- [Photometry - KIL_VML3X2830NDR](#)
- [Photometry - KIL_VML3X2830N](#)
- [Specifications - WML3X2830D4G Specification Sheet French](#)
- [Specifications - WML3X2830D4G Specification Sheet English](#)