



XAS Series - Aluminum Feed-Thru Fire Alarm Station With Breaking-Glass Activation - Hub Size 3/4 Inch Npt - 1NO/1NC Contact Rating

By Killark
Catalog # XAS-53



XAS Series - Aluminum Feed-Thru Fire Alarm Station With Breaking-Glass Activation - Hub Size 3/4 Inch Npt - 1NO/1NC Contact Rating.

General

Action	SP
Actuator	Break Glass
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Application	
Back Box Type	SWB
Catalog Number	XAS-53
Color	
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	1
Series	XAS
Type	
UPC	783936880396

Dimensions

Depth	4-1/16
Dimensions	8.25 in x 5.75 in x 6.75 in
Gross Weight with Packaging	3
Height	6.75 in
Length	8.25 in
Width	5.75 in

Electrical Ratings

Amperage Rating	10 A
Contact Rating	7200 VA (make), 720 VA (break), 10A cont. @ 600V AC; 2.5A cont. @ 600V DC.
Frequency Rating	50/60 Hz

Certifications And Compliance

CSA File Number	LR31085
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D Class I, Zones 1 & 2, Groups IIB, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
UL File Number	E50498

Product Assets

- [Certifications - XAS Series Fire Alarm UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - XAS Series IOM K0542](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-XAS53-SPEC-EN | REV 6/2024