



By Killark  
Catalog # [XCS-0A8](#)

XCS Series- Cover with Device - Momentary Contact Three Mini Red-Green-Black Push Buttons



Features

- Copper free cast aluminum alloy.
- Ground flange joint between bolted cover and box provide required flame path.
- Push button, selector switches and pilot light operator bodies are copper-free aluminum.
- Operating shaft in both push buttons and selector switches are stainless steel.

Application

Hazardous locations due to the presence of flammable gases or vapors, combustible dusts, or easily ignitable fiber or flyings. Installations at petroleum refineries, chemical and petrochemical plants, and other processing or storage facilities where simil

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR11714
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D;Class I, Zones 1 & 2, Groups IIB, IIA;Class II, Divisions 1 & 2, Groups E, F, G;Class III, Divisions 1 & 2
UL File Number	E53360

Configuration

Back Box Type	SWB
Number Of Poles	3

Current

Amperage Rating	10 A
Frequency Rating	50/60 Hz

Contact Rating

60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A INRUSH @ 600 VAC; 6A BREAKING @ 120 VAC; 3A BREAKING @ 240 VAC; 1.5A BREAKING @ 480 VAC; 1.2A BREAKING @ 600 VAC; 10A CARRYING @ 120 VAC; 10A CARRYING @ 240 VAC; 10A CARRYING @ 480 VAC;

Dimensions

Depth	1-3/4
Length	6.88 in
Gross Weight with Packaging	1.5
Width	3.75 in
Height	5.5 in
Dimensions	6.88 in x 3.75 in x 5.5 in

General

Series	XCS
Color	Green, Red, Black
Type	Aluminum Cover With Three Mini Push Buttons
Material	Copper-free aluminum
UPC	783936890463

Operational

Action	SP (per circuit)
Actuator	Momentary Pushbutton

Product Assets

[Installation Manual \[French, English\]](#)