



XCS-OB24-RL

By Killark
Catalog # [XCS-OB24-RL](#)

XCS Series - Aluminum 120V Pilot Light Cover With Device - Red Lens With Nameplate To Be Specified

Features

- Copper free cast aluminum alloy.
- Ground flange joint between bolted cover and box provide required flame path.
- Push button, selector switches and pilot light operator bodies are copper-free aluminum.
- Operating shaft in both push buttons and selector switches are stainless steel.

Application

Hazardous locations due to the presence of flammable gases or vapors, combustible dusts, or easily ignitable fiber or flyings. Installations at petroleum refineries, chemical and petrochemical plants, and other processing or storage facilities where simi

General

Actuator	Pilot Light
Back Box Type	SWB
Catalog Number	XCS-OB24-RL
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	XCS
Type	Aluminum Cover With Pilot Light
UPC	783936890128

Dimensions

Depth	2-3/32
Dimensions	7.5 in x 5.875 in x 4.25 in



Gross Weight with Packaging	1.2
Height	4.25 in
Length	7.5 in
Width	5.875 in

Electrical Ratings

Amperage Rating	0.25 A
Frequency Rating	50/60 Hz

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
UL File Number	E53360

Product Assets

- [Certifications - FXCS & XCS Series Auxiliary Devices UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SWB SeriesControl Stations IOM K0569F](#)
- [Specifications - XCS-OB24-RL Specification Sheet French](#)
- [Specifications - XCS Series Cover Assemblies Control Stations Specification Sheet](#)
- [Specifications - XCS0B24RL Specification Sheet English](#)