



**XCS-OB4 - XCS Series, AL
Momentary Contact Double Push
Button Cvr w/ Device, Green Button
w/ Start Nameplate, Red Button w/
Stop Nameplate, 1NO/1NC**

By Killark
Catalog # [XCS-OB4](#)



*Representative Image

XCS Series - Aluminum Momentary Contact Double Push Button
Cover With Device - Green Button With "Start" Nameplate - Red
Button With "Stop" Nameplate - 1NO/1NC Contact Rating

Features

-
-
-
-

General

Action	SP (per circuit)
Actuator	Momentary Pushbutton
Back Box Type	SWB
Catalog Number	XCS-OB4
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Number Of Poles	2
Series	XCS
UPC	783936890081

Dimensions

Depth	1-3/4
Dimensions	6.375 in x 6 in x 4.375 in
Gross Weight with Packaging	1.33
Height	4.375 in
Length	6.375 in
Width	6 in

Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A

INRUSH @ 480 VAC; 12A
INRUSH @ 600 VAC; 6A
BREAKING @ 120 VAC; 3A
BREAKING @ 240 VAC; 1.5A
BREAKING @ 480 VAC; 1.2A
BREAKING @ 600 VAC; 10A
CARRYING @ 120 VAC; 10A
CARRYING @ 240 VAC; 10A
CARRYING @ 480 VAC;
50/60 Hz

Frequency Rating

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
UL File Number	E53360

Product Assets

- [Certifications - FXCS & XCS Series Auxiliary Devices UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SWB Series Control Stations IOM K0569F](#)
- [Specifications - XCS-OB4 Specification Sheet French](#)
- [Specifications - XCS Series Cover Assemblies Control Stations Specification Sheet](#)
- [Specifications - XCSOB4 Specification Sheet English](#)