



XCS-0K2A1 - XCS Series, AL
Maintained Contact 2-Pos Keyed
Selector Switch Cvr w/ Device,
Keyed Diff w/ Removal Both, Off-
On Nameplate, 1NO/1NC Contact

By Killark
Catalog # [XCS-0K2A1](#)



*Representative Image

XCS Series - Aluminum Maintained Contact 2-Position Keyed
Selector Switch Cover With Device - Keyed Different With Key
Removal In Both Positions- "Off - On" Nameplate - 1NO/1NC
Contact Rating

Features

-
-
-
-

General

Action	Rotary
Actuator	2 Position Selector Switch
Back Box Type	SWB
Catalog Number	XCS-0K2A1
Color	Black
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Number Of Poles	1
Series	XCS
UPC	783936890432

Dimensions

Depth	2-3/4
Dimensions	7.625 in x 5.875 in x 4.125 in
Gross Weight with Packaging	1.63
Height	4.125 in
Length	7.625 in
Width	5.875 in

Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A

INRUSH @ 480 VAC; 12A
INRUSH @ 600 VAC; 6A
BREAKING @ 120 VAC; 3A
BREAKING @ 240 VAC; 1.5A
BREAKING @ 480 VAC; 1.2A
BREAKING @ 600 VAC; 10A
CARRYING @ 120 VAC; 10A
CARRYING @ 240 VAC; 10A
CARRYING @ 480 VAC;
50/60 Hz

Frequency Rating

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
UL File Number	E53360

Product Assets

- [Certifications - FXCS & XCS Series Auxiliary Devices UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_XCS0K Spring Return Keyed Selector Switch Assemblies IOM_K0565](#)
- [Installation Manuals - SWB SeriesControl Stations IOM K0569F](#)
- [Specifications - XCS0K2A1 Specification Sheet English](#)
- [Specifications - XCS Series Cover Assemblies Control Stations Specification Sheet](#)