



**XCS-OMMR3 - XCS Series, AL
Maintained Contact Push/Pull
Button Cvr w/ Device, Red
Mushroom w/ 3 Nameplates
Start/Stop, Blank, Emergency Stop,
1NO/1NC**

By Killark
Catalog # [XCS-OMMR3](#)

XCS Series - Aluminum Maintained Contact Push/Pull Button
Cover With Device - Red Mushroom Button Supplied With Three
Nameplates("Start/Stop", Blank, "Emergency Stop") - 1NO/1NC
Contact Rating

Features

-
-
-
-
-

General

Action	SP
Actuator	Maintained Pushbutton
Back Box Type	SWB
Catalog Number	XCS-OMMR3
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Number Of Poles	1
Series	XCS
UPC	783936890401

Dimensions

Depth	3-1/8
Dimensions	5.56 in x 4 in x 5.63 in
Gross Weight with Packaging	1.4
Height	5.63 in
Length	5.56 in
Width	4 in

Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A INRUSH @ 600 VAC; 6A



*Representative Image

BREAKING @ 120 VAC; 3A
BREAKING @ 240 VAC; 1.5A
BREAKING @ 480 VAC; 1.2A
BREAKING @ 600 VAC; 10A
CARRYING @ 120 VAC; 10A
CARRYING @ 240 VAC; 10A
CARRYING @ 480 VAC;
50/60 Hz

Frequency Rating

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
UL File Number	E53360

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Certifications - FXCS & XCS Series Auxiliary Devices UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - XCS0MMR3 Specification Sheet English](#)
- [Specifications - XCS-OMMR3 Specification Sheet French](#)
- [Specifications - XCS Series Cover Assemblies Control Stations Specification Sheet](#)