



XCS Series Control Station Cover - Maintained Contact 2-Position Selector Switch Cover With Device - "Off - On" Nameplate - 1NO/1NC Contact Rating

By Killark
Catalog # [XCS-OS2A1](#)



*Representative Image

XCS Series - Aluminum Maintained Contact 2-Position Selector Switch Cover With Device - "Off - On" Nameplate - 1NO/1NC Contact Rating

Features

-
-
-
-

General

Action	Rotary
Actuator	2 Position Selector Switch
Back Box Type	SWB
Catalog Number	XCS-OS2A1
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Number Of Poles	1
Series	XCS
UPC	783936890135

Dimensions

Depth	3-5/16
Dimensions	6.875 in x 5.75 in x 4.75 in
Gross Weight with Packaging	1.52
Height	4.75 in
Length	6.875 in
Width	5.75 in

Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A

INRUSH @ 480 VAC; 12A
INRUSH @ 600 VAC; 6A
BREAKING @ 120 VAC; 3A
BREAKING @ 240 VAC; 1.5A
BREAKING @ 480 VAC; 1.2A
BREAKING @ 600 VAC; 10A
CARRYING @ 120 VAC; 10A
CARRYING @ 240 VAC; 10A
CARRYING @ 480 VAC;
50/60 Hz

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
UL File Number	E53360

Product Assets

- [Certifications - FXCS & XCS Series Auxiliary Devices UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SWB SeriesControl Stations IOM K0569F](#)
- [Specifications - XCS0S2A1 Specification Sheet English](#)
- [Specifications - XCS Series Cover Assemblies Control Stations Specification Sheet](#)