



XECF-604A3 - XEC Series,60 Amp, 240/480 VAC, 3 Pole, EHD Frame, Circuit Breaker Enclosure

By Killark
Catalog # [XECF-604A3](#)

XEC Series,60 Amp, 240/480 VAC, 3 Pole, EHD Frame, Circuit Breaker Enclosure

Features

-
-
-
-
-
-
-

Application

XEC Series hazardous areas due to the the presence of flammable gases or vapors, combustible dusts, or easily ignitable fibers or flyings. Provides overcurrent and short circuit protection.

General

Action	TP
Actuator	Molded Case Circuit Breaker Operator
Catalog Number	XECF-604A3
Color	Aluminum
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Bolted
Finish Type	Lacquer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Wall
Number Of Poles	3
Operating Temperature Celcius Max	40 Degree
Series	XEC
Type	Circuit Breaker Enclosure
UPC	783936896335



Dimensions

Depth	7
Height	16 in
Weight	20 lb
Width	7.75 in

Electrical Ratings

Amperage Rating	60 A
Frequency Rating	60 Hz
Primary Voltage	480 VAC/250 VDC

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

CSA File Number	LR18179
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
Nema Rating	7 (B, C, D), 9 (E, F, G)
UL File Number	E30962

Product Assets

- [Customer Notices - Prop 65 Notice](#)
[Specifications - XEC Series Circuit Breakers Specification Sheet](#)
[Specifications - XECF-604A3 Specification Sheet French](#)
[Specifications - XECF604A3 Specification Sheet English](#)