



XEDS-100A - XEDS Series, 100 Amp Max, Non-Fused Disconnect Switch W/ 1 Aux Contact

By Killark

Catalog # [XEDS-100A](#)

XEDS Series, 100 Amp Max, Non-Fused Disconnect Switch W/ 1 Aux Contact.



*Representative Image

General

Catalog Number	XEDS-100A
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Bolted
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Number Of Poles	3
Operating Temperature Celcius Max	40 Degree
Series	XEDS
Type	
UPC	783936898094

Dimensions

Depth	7
Height	16 in
Weight	17 lb
Width	9.125 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 VAC/250 VDC

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
Nema Rating	3R, 4, 9(E, F, G)
UL File Number	E53290

Product Assets

[Certifications - DEDS & XEDS Series UL Certification](#)

[Customer Notices - Prop 65 Notice](#)



A Hubbell brand