



XEDS-30 - XEDS Series, 30 Amp Disconnect Switch

By Killark
Catalog # [XEDS-30](#)

XEDS Series, 30 Amp Disconnect Switch

Features

- External handle is vault type with standard provisions for locking in "OFF" position with up to three padlocks.
- Provisions for locking in "ON" position available as factory modification (add suffix SU40 to catalog number).
- Enclosure and external handle is cast copper-free aluminum alloy (less than 4/10 of 1%).
- Cover bolts are stainless steel.
- Eaton (Cutler Hammer) Type DS Switches.
- Two cast conduit hubs, one top and one bottom.
- Internal disconnect handle mechanism is a sliding plate mounted to the cover.

General

Catalog Number	XEDS-30
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Bolted
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Wall
Number Of Poles	3
Operating Temperature Celcius Max	40 Degree
Series	XEDS
UPC	783936897981

Dimensions



*Representative Image

Depth	6.875
Height	11.875 in
Weight	11 lb
Width	8.75 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 VAC/250 VDC

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	3R, 4, 9(E, F, G)
UL File Number	E53290

Product Assets

- [Certifications - DEDS & XEDS Series UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - XEDS30 Specification Sheet English](#)
- [Specifications - XEDS-30 Specification Sheet French](#)
- [Specifications - XEDS Series Disconnect Switches Specification Sheet](#)