



XMSW-1CT - Manual Motor Starter - NEMA Size 1 - 3-Pole; 3Ø, Ac

By Killark
Catalog # [XMSW-1CT](#)

Manual Motor Starter - NEMA Size 1 - 3-Pole; 3Ø, Ac

Features

- Rectangular bolted cover design provides for attractive, compact, uniform installations.
- Enclosure and external handle are diecast copper-free (less than 0.4%) aluminum alloy.
- Cast “ON,” “OFF,” “TRIPPED” markings on cover align with external handle and provide clear indication of enclosed starter condition.
- External handle is a vault type with standard provisions for locking in the “OFF” position with up to three pad-locks.
- Provision for locking in “ON” position is available as factory modification (add suffix SU-40 to catalog number).
- Two cast 1” NPT conduit hubs with integral pipe stop, one top and one bottom, are standard on all assemblies.

General

| | |
|----------------------|----------------------|
| Catalog Number | XMSW-1CT |
| EU RoHS Indicator | Contact Manufacturer |
| Horsepower - Maximum | 10 |
| Series | XMSW |
| Size | 1 |
| UPC | 783936912585 |



Electrical Ratings

| | |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

Certifications And Compliance

| | |
|---------------------|--|
| Hazardous Rating(s) | <ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2 |
| UL File Number | E12379 |

Product Assets

- [Certifications - XMSW Series UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - XMSW-1CT Specification Sheet French](#)
- [Specifications - XMSW1CT Specification Sheet English](#)
- [Specifications - XMSW Series Manual Motor Starters Specification Sheet](#)