

# XSD-51 - XSD/XSX/FXSD/FXSX Series - XSD Single Gang Aluminum Manual Motor Starting Switch - 1 Pole Single Phase - Feed-Thru - Hub Size 3/4 In

By Killark

Catalog # [XSD-51](#)

XSD/XSX/FXSD/FXSX Series - XSD Single Gang Aluminum Manual Motor Starting Switch - 1 Pole Single Phase - Feed-Thru - Hub Size 3/4 In

## Features

- Motor running protection when overload heaters are used.
- Enclosures are cast copper-free aluminum alloy.
- Operating shaft is stainless steel.
- Multiple gang assemblies available in combination with pilot lights, pushbuttons and switches on request.
- Ground flange joint between bolted cover and box provide required flame path.
- Provisions for padlocking switch in either "ON" or "OFF" position is standard.

## General

Catalog Number	XSD-51
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	1
Material	Copper-free aluminum
Series	XSD
UPC	783936932170

## Dimensions

Dimensions	3 in x 4 in x 6 in
Gross Weight with Packaging	2.4
Height	6 in
Length	3 in
Width	4 in



\*Representative Image

## Electrical Ratings

Frequency Rating	60 Hz
Power Factor	0.9
Voltage Rating	230 V

## Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
UL File Number	E53360 / E12379

## Product Assets

Certifications - FXS & XS Series Motor Starters UL Certification
Customer Notices - Prop 65 Notice
Installation Manuals - SWB Series Control Stations IOM K0569F
Specifications - XSD51 Specification Sheet English
Specifications - XSD-51 Specification Sheet French
Specifications - XSD/XSX & FXSD/FXSX Series Manual Motor Starters Specification Sheet