



# Y-5M-EX - 90° 1-1/2" Iron, Capped Elbow (Quad Listed)

By Killark  
Catalog # [Y-5M-EX](#)

90° 1-1/2" Iron, Capped Elbow (Quad Listed).



\*Representative Image

## Features

- Threaded for rigid conduit or IMC
- Smooth integral bushings to prevent damage to wires
- Certified QUAD listed

## Application

To change direction 90° in rigid or IMC conduit systems where space is limited and access is needed for pulling conductors or maintenance.

## General

Color	<ul style="list-style-type: none"><li>• Gray</li><li>• Gris</li></ul>
Cover Type	Threaded
Finish Type	Powder Epoxy Paint
Material	Iron
Series	Y
Type	<ul style="list-style-type: none"><li>• Capped Elbow</li><li>• Capped Elbow</li></ul>
UPC	783936072593

## Dimensions

Diameter - Inside	0.55 in
Dimensions	6 in x 4 in x 5 in
Gross Weight with Packaging	3.89
Height	5 in
Hub Size	1-1/2"
Length	6 in
Width	4 in

## Certifications and Compliance

ATEX File Number	ITS09ATEX16417U
CSA File Number	LR11716
Hazardous Rating(s)	II2GEx d IIC
IECEX File Number	IECEXITS09.0024U
UL File Number	E10514

## Logistics

Carton Quantity	2
-----------------	---

## Product Assets

[Certifications - BL & Y Series Elbows UL Certification](#)  
[Certifications - Elbows & Union UKCA Certificate](#)  
[Certifications - Elbows & Union ATEX Certificate](#)  
[Certifications - Elbows & Unions IECEx Certification](#)  
[Certifications - Y Series CSA Certification](#)  
[Certifications - EX Series Elbows & Unions Declaration of Conformity](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - ATEX Elbows & Unions IOM K1435](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-Y-5M-EX-SPEC-EN | REV 1/2024