



ZN208CR - 3/4" Nylon Cord Connector, 90° Bend, Cord Range .375-.500, Blue

By Killark
Catalog # [ZN208CR](#)

3/4" Nylon Cord Connector, 90° Bend, Cord Range .375-.500, Blue.



*Representative Image

Features

- Nylon retention ring for increased holding power
- Neoprene bushing seals against moisture
- Nylon connectors obtain approximately the same retention values as metal cord connectors

Application

Durable nylon construction makes these connectors perfectly suited to corrosive environments. Typical applications for nylon cord connectors include food processing facilities, chemical and sewage treatment plants, and off-shore and dockside installations

General

Color	<ul style="list-style-type: none">• Gray• Gris
Color Code	Blue
Cord Range	.375-.500,
Finish Type	Natural
Material	Nylon
Series	Z Series
Type	<ul style="list-style-type: none">• 90° Cord Connector• 90° Cord Connector
UPC	783936989853

Dimensions

Dimensions	2 in x 1 in x 3 in
Gross Weight with Packaging	0.12
Height	3 in
Hub Size	3/4"
Length	2 in
Width	1 in

Conductor Related

Cable Range	.375 - .500 in
-------------	----------------

Certifications and Compliance

CSA File Number	LR73478
UL File Number	E22698

Logistics

Carton Quantity	15
-----------------	----

Product Assets



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-ZN208CR-SPEC-EN | REV 1/2024