



ZN208ZP - 3/4" Steel (Zinc Plated) 90° Cord Connector, Cord Range .375-.500, Blue

By Killark
Catalog # ZN208ZP



3/4" Steel (Zinc Plated) 90° Cord Connector, Cord Range
.375-.500, Blue.

*Representative Image

Features

- Neoprene grommet seals out oil and moisture
- Nylon retention ring incorporates a splithinge design to prevent friction and provide strain relief, also color-coded for sizing identification
- These heavy-duty connectors hold up to most manufacturing chemicals including, acid solutions, solvents and other corrosive materials
- Machined steel nut, malleable iron body allows for tightening the compression nut and NPT hub without worrying about stripping the threads

General

Catalog Number	ZN208ZP
Color	Silver
	Argent
EU RoHS Indicator	Contact Manufacturer
Finish Type	Naturel
Material	Steel
Series	Z Series
Type	
UPC	783936121000

Dimensions

Dimensions	1.88 in x 0.56 in x 2.9 in
Gross Weight with Packaging	0.55
Height	2.9 in
Hub Size	3/4"
Length	1.88 in
Width	0.56 in

Conductor Related

Cable Range	.375 - .500 in
-------------	----------------

Certifications And Compliance

CSA File Number	LR73478
Nema Rating	4, 4X, 12, 13
UL File Number	E22698

Logistics

Carton Quantity	15
-----------------	----

Product Assets

[Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-ZN208ZP-SPEC-EN | REV 6/2024