



ZS311CR-EX-MG - 1" Nylon Cord Connector, Straight w/ Mesh Grip, Cord Range .750-.875, Purple

By Killark
Catalog # [ZS311CR-EX-MG](#)



1" Nylon Cord Connector, Straight w/ Mesh Grip, Cord Range .750-.875, Purple.

*Representative Image

Features

- Nylon retention ring for increased holding power
- Neoprene bushing seals against moisture
- Nylon connectors obtain approximately the same retention values as metal cord connectors
- Stainless steel mesh grips resist corrosion, prevent cord pull-out and control arc-of-bend

General

Application	
Catalog Number	ZS311CR-EX-MG
Color	Black, Gray Gris-Noir
Color Code	Purple
Cord Range	.750-.875,
EU RoHS Indicator	Contact Manufacturer
Finish Type	Naturel
Material	Nylon
Series	Z Series EX
Type	
UPC	783936996615

Dimensions

Dimensions	2 in x 1 in x 2 in
Gross Weight with Packaging	0.2
Height	2 in
Hub Size	1"
Length	2 in
Width	1 in

Electrical Ratings

Frequency Rating	60 Hz
Power Factor	0.9

Conductor Related

Cable Range	.750 - .875 in
-------------	----------------

Certifications And Compliance

CSA File Number	LR73478
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E22698

Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-ZS311CREXMG-SPEC-EN | REV 6/2024