



# VM4LB6IE230 - VM4LB 6000 Lumen Range Standard with 2000 Lumen Battery Backup 120-277VAC 50/60 Hz

By Killark  
Catalog # [VM4LB6IE230](#)



VM4LB 6000 Lumen Range Standard with 2000 Lumen Battery Backup 120-277VAC 50/60 Hz

## General

Catalog Number	VM4LB6IE230
Color Temperature	5000 K
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	5,001-10,000 lm
Lumens	6278
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Operating Temperature Range Celcius	-20°C to +50°C

Series	VM4L
UPC	783936151731

## Electrical Ratings

Lumens Per Watt	157
Voltage Rating	120-277 VAC
Wattage	40 W

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Specifications - VM4LB6IE230](#)