

3-5/8" (92mm) diameter viewing window while maintaining the compact body diameter of 5" (127mm)

> Smooth die cast finish with gray powder paint for an aesthetically pleasing look to a OEM product - other colors available - contact factory.

Die cast from 413 aluminum alloy, copper free and low magnesium content.

Recessed cross notches for wrenching when required

Large recess grip slots for opening and closing of cover even while wearing heavy gloves.

Cover locking set screw standard in all covers. Prevents tampering and unauthorized access to the internal components.

Internal pad for additional openings through the back wall can be drilled and tapped; 1/2" NPT or NPSM, 3/4" NPT or NPSM, M20, M25

Large "X" pad which will accept any diameter bolt circle

Large straight internal opening, 4-1/4" (108mm) diameter with a full depth - no wasted space

Standard with three 3/4 NPTs openings. Optional sizes, 3/4" NPSM and M25 can be special ordered.

Large wire way opening for ease of wire pull in the field.

Anti-turn Internal
Ground Screw
Assembly Standard

Anti-turn external
Ground Screw
Assembly Standard

O-ring gasket for a Type 3, 4 IP66 environment rating

Mounting lugs with 1/4" (6.3mm) dia. mounting holes supplied as a standard

HKBX SERIES





HKBX

Empty Enclosure

NEC / CEC Certifications

Class I, Groups A, B, C & D
Class I, Zone 1, AEx db IIC
Class II, Groups E, F & G
Class III
Type 3, 4, 4X
Ta = -60°C to +70°C (UL & CSA)
Ta = -20°C to +40°C (FM)

Files E83969 E150827

File LR11716 - 1750685

ATEX / IEC Ex Certificate

No series in the series in th





FEATURES-SPECIFICATIONS

Features

- Enclosures are explosion / flame proof, dust / ignition proof, weather / hose down proof and tamper resistant.
- ATEX & IEC Ex standard on all assemblies.
- HKBX Series box and covers are die cast from copper-free aluminum.
- Neoprene O-ring provide as standard to assure water resistance in Type 3, 4 / IP66 conditions
- Large viewing, 3-5/8"(92mm) diameter.
- Large 4-1/4"(108mm) diameter internal cover opening with a full depth - no wasted space.
- HKBX box has offset feed through conduit openings, three 3/4" NPTs supplied as standard. Optional 3/4" NPSM or M25 openings available.
- A large internal mounting pad supplied in a "X" configuration for the flexibility of adapting to any OEM bolt circle.

- Both a internal and external anti-turn ground (earth) terminals supplied as standard.
- All covers supplied standard with shrouded tamper resistant set screw.
- Recessed cover lugs permit easy removal and tightening. Large recess grip slots for opening and closing of the cover.
- Cast on mounting lugs standard 1/4" (6.3mm) Dia. Mounting Holes.
- Same mounting foot print as the legacy HKB Series boxes.

Materials

- HKBX Series box and covers are die cast from 413 copper-free aluminum, containing less than 4/10 of 1% alloy and less than 6% magnesium.
- O-ring gasket Neoprene (70 durometer nitrile compound)
- Ground (earth) screw 316 Stainless steel with green plating.
- Allen head cover locking screw 316 Stainless steel
- Glass lens 3/8"(9.5mm) thick tempered float glass.
- Finish silver powder epoxy paint electrostatically applied.
- · Special colors available in quantity

Factory / Field Modifications

- UL & CSA approvals allow for the field drilling and tapping of blind holes into the internal "X" ribs for mounting of customer equipment. The internal pad allows for the field drilling and tapping for one additional opening, 1/2" NPT or NPSM, 3/4" NPT or NPSM, or M20 or M25.
- ATEX IEC Ex approvals all machining modifications must be done by the factory.





CATALOG LOGIC

нквх-BC-**Back Box - Series Constant** Cover Type **HKBX** Blank - No Cover - Box Only

BC - Blank Flat Cover - HFCX

GLC - Lens Flat Cover - HKXGL 2DC - Blank 2" Dome Cover - HKX2D

2GLDC - Lens 2" Dome Cover - HKX2GLD

Back Wall Additional **Openings - Optional**

10 - 1/2" NPT 1s - 1/2" NPSM

20 - 3/4" NPT

Ø3.62

2.00 [50.8]

2s - 3/4" NPSM M20 - M20 Metric Straight

M25 - M25 Metric Straight

*** (Contact Factory For Availability) Side Hub Alternate Openings

2s - 3/4" NPSM

M25 - M25 Metric Straight

MX - Mix of Sizes


| HKBX COMPONENT AND ASSEMBLY NUMBERS | | |
|-------------------------------------|--|--|
| CATALOG NUMBER | ITEM DESCRIPTION | |
| HKBX | Box only 4-1/4" (108mm) internal diameter opening | |
| HFCX | Flat cover 4-1/4" (108mm) internal diameter opening | |
| HKXGL | Lens cover 3-5/8" (92mm) diameter viewing | |
| HKX2D | Dome 2" cover 4-1/4" (108mm) internal diameter | |
| HKX2GLD | Dome 2" lens cover 3-5/8" (92mm) diameter viewing | |
| HKBX-BC | Box with flat cover 4-1/4" (108mm) internal diameter QUAD Approvals | |
| HKBX-GLC | Box with lens cover 3-5/8" (92mm) viewing QUAD Approvals | |
| HKBX-2DC | Box with 2" dome cover 4-1/4" (108mm) internal diameter QUAD Approvals | |
| HKBX-2GLDC | Box with 2" dome lens cover 3-5/8" (92mm) viewing QUAD Approvals | |
| HKBX-GRD | HKBX replacement ground kit | |
| 15722JABB | HKBX replacement "O" ring | |


| Motor The UVDV | covers are non-interchangeable with the legacy HKR's covers | |
|----------------|---|--|
| | | |

| HKBX FACTORY MODIFICATIONS | | | | |
|----------------------------|---|--|--|--|
| OPTIONAL FACTORY MACHINING | | | | |
| CATALOG SUFFIX | MODIFICATION DESCRIPTION | | | |
| -10 | 1/2" NPT in the back wall | | | |
| -1\$ | 1/2" NPSM in the back wall | | | |
| -20 | 3/4" NPT in the back wall | | | |
| -2\$ | 3/4" NPSM in the back wall | | | |
| -288 | 3/4" NPSM in the side hubs Consult Factory for Pricing | | | |
| -M20 | M20 in the back wall | | | |
| -M25 | M25 in the back wall | | | |
| -M25S | M25 in the side hubs Consult Factory for Pricing | | | |
| -MX | Mix of sizes and locations Consult Factory for Pricing | | | |

6.19 5.50 [157.2] [139.7] MNT'G

HOLES





2.00

[50.8]


0

ENCLOSUE

HKBX-TB SERIES



HKBX TERMINAL BOX - UL / CSA / ATEX / IEC EX





HKBX TERMINAL BOX - UL / CSA / ATEX / IEC EX





HKBX-TB

Terminal Box

NEC / CEC Certifications

Class I, Groups A, B, C & D Class I, Zone 1, AEx db IIC Class II, Groups E, F & G Class III Type 3, 4, 4X $Ta = -60^{\circ}C \text{ to } +70^{\circ}C$

File E83969

® File LR11716 - 1750685

ATEX / IEC Ex Certificate

II 2 G D € 2813 Ex db IIC T4...T3 Gb Ex eb IIC T4...T3 Gb Ex tb IIIC T110°C...T140°C IP66 Ta = -60°C to +70°C **DEMKO 06ATEX 141023X DEMKO 06ATEX 0521635X IECEX UL 14.0060X IECEX UL 14.0069X**

FEATURES-SPECIFICATIONS

Features

- Maximum (10) 2.5mm2 terminal blocks
- Maximum 630VAC, 60 AMPs
- Enclosures are explosion / flame proof, dust / ignition proof, weather / hose down proof and tamper resistant.
- ATEX & IEC Ex standard on all assemblies.
- Box and cover without ATEX IEC Ex can be sold separately.
- HKBX Series box and covers are die cast from copper-free aluminum.
- Neoprene O-ring provide as standard to assure water resistance in Type 3, 4 / IP66 conditions
- Large 4-1/4" (108mm) diameter internal cover opening with a full depth - no wasted space.
- HKBX box has offset feed through conduit openings, three 3/4" NPTs supplied as standard. Optional 3/4" NPSM or M25 openings available.
- A large internal mounting pad supplied in a "X" configuration for the flexibility of adapting to any OEM bolt circle.

- Both a internal and external anti-turn ground (earth) terminals supplied as standard.
- Cover supplied standard with shrouded tamper resistant set screw.
- Recessed cover lugs permit easy removal and tightening. Large recess grip slots for opening and closing of the cover.
- Cast on mounting lugs standard 1/4" (6.3mm) Dia. Mounting Holes.
- Same mounting foot print as the legacy HKB Series boxes.

Materials


- HKBX Series box and covers are die cast from 413 copper-free aluminum. containing less than 4/10 of 1% alloy and less than 6% magnesium.
- O-ring gasket Neoprene (70 durometer nitrile compound)
- Ground (earth) screw 316 Stainless steel with green plating.
- Allen head cover locking screw 316 Stainless steel
- Finish silver powder epoxy paint electrostatically applied
- Special colors available in quantity





ENCLOSUF





| REPLACEMENT COMPONENTS | | |
|------------------------|-----------------------------|--|
| CATALOG NUMBER | DESCRIPTIONS | |
| HKBX-GRD | HKBX replacement ground kit | |
| 15722AAAB | HKBX replacement "O" ring | |

Note: The HKBX covers are non-interchangeable with the legacy HKB's covers.

| HKBX FACTORY MODIFICATIONS | | | | |
|----------------------------|---|--|--|--|
| OPTIONAL FACTORY MACHINING | | | | |
| CATALOG SUFFIX | MODIFICATION DESCRIPTION | | | |
| -2\$\$ | 3/4" NPSM in the side hubs Consult Factory for Pricing | | | |
| -M25\$ | M25 in the side hubs Consult Factory for Pricing | | | |
| -MX | Mix of sizes and locations Consult Factory for Pricing | | | |