



CROSS REFERENCE

ALUMINUM			IRON		
KILLARK O SERIES	APPLETON FORM 85™ UNILETS™	CROUSE-HINDS CONDULET® SERIES 5	KILLARK DURALOY® 5	APPLETON FORM 35™	CROUSE-HINDS FORM 5
LB			LB		
OLB-1	LB-50A	LB15	OLB-1M	LB-50M	LB50M
OLB-2	LB-75A	LB25	OLB-2M	LB-75M	LB75M
OLB-3	LB-100A	LB35	OLB-3M	LB-100M	LB100M
OLB-4	LB-125A	LB45	OLB-4M	LB-125M	LB125M
OLB-5	LB-150A	LB55	OLB-5M	LB-150M	LB150M
OLB-6	LB-200A	LB65	OLB-6M	LB-200M	LB200M
OLB-7	LB-250A	LB75	OLB-7M	LB-250M	LB250M
OLB-8	LB-300A	LB85	OLB-8M	LB-300M	LB300M
OLB-9	LB-350A	LB95	OLB-9M	LB-350M	LB350M
OLB-0	LB-400A	LB105	OLB-0M	LB-400M	LB400M
LB COVER GASKET			LB COVER GASKET		
OLB-1CG	LB-50ACGA	LB15CGN	OLB-1MCG	-	LB50MCG
OLB-2CG	LB-75ACGA	LB25CGN	OLB-2MCG	-	LB75MCG
OLB-3CG	LB-100ACGA	LB35CGN	OLB-3MCG	-	LB100MCG
OLB-4CG	LB-125ACGA	LB45CGN	OLB-4MCG	-	LB125MCG
OLB-5CG	LB-150ACGA	LB55CGN	OLB-5MCG	-	LB150MCG
OLB-6CG	LB-200ACGA	LB65CGN	OLB-6MCG	-	LB200MCG
OLB-7CG	-	LB75CGN	OLB-7MCG	-	LB250MCG
OLB-8CG	-	LB85CGN	OLB-8MCG	-	LB300MCG
OLB-9CG	-	LB95CGN	OLB-9MCG	-	LB350MCG
OLB-0CG	-	LB105CGN	OLB-0MCG	-	LB400MCG
C			C		
OC-1	C-50A	C15	OC-1M	C-50M	C50M
OC-2	C-75A	C25	OC-2M	C-75M	C75M
OC-3	C-100A	C35	OC-3M	C-100M	C100M
OC-4	C-125A	C45	OC-4M	C-125M	C125M
OC-5	C-150A	C55	OC-5M	C-150M	C150M
OC-6	C-200A	C65	OC-6M	C-200M	C200M
OC-7	C-250A	C75	OC-7M	C-250M	C250M
OC-8	C-300A	C85	OC-8M	C-300M	C300M
OC-9	C-350A	C95	OC-9M	C-350M	C350M
OC-0	C-400A	C105	OC-0M	C-400M	C400M
C COVER GASKET			C COVER GASKET		
OC-1CG	C-50ACGA	C15CGN	OC-1MCG	-	C50MCG
OC-2CG	C-75ACGA	C25CGN	OC-2MCG	-	C75MCG
OC-3CG	C-100ACGA	C35CGN	OC-3MCG	-	C100MCG
OC-4CG	C-125ACGA	C45CGN	OC-4MCG	-	C125MCG
OC-5CG	C-150ACGA	C55CGN	OC-5MCG	-	C150MCG
OC-6CG	C-200ACGA	C65CGN	OC-6MCG	-	C200MCG
OC-7CG	-	C75CGN	OC-7MCG	-	C250MCG
OC-8CG	-	C85CGN	OC-8MCG	-	C300MCG
OC-9CG	-	C95CGN	OC-9MCG	-	C350MCG
OC-0CG	-	C105CGN	OC-0MCG	-	C400MCG



KILLARK

ALUMINUM			IRON		
KILLARK O SERIES	APPLETON FORM 85™ UNILETS™	CROUSE-HINDS CONDULET® SERIES 5	KILLARK DURALOY® 5	APPLETON FORM 35™	CROUSE-HINDS FORM 5
LL			LL		
OLL-1	LL-50A	LL15	OLL-1M	LL-50M	LL50M
OLL-2	LL-75A	LL25	OLL-2M	LL-75M	LL75M
OLL-3	LL-100A	LL35	OLL-3M	LL-100M	LL100M
OLL-4	LL-125A	LL45	OLL-4M	LL-125M	LL125M
OLL-5	LL-150A	LL55	OLL-5M	LL-150M	LL150M
OLL-6	LL-200A	LL65	OLL-6M	LL-200M	LL200M
OLL-7	L-250A	LL75	OLL-7M	LL-250M	LL250M
OLL-8	LL-300A	LL85	OLL-8M	LL-300M	LL300M
OLL-9	LL-350A	LL95	OLL-9M	LL-350M	LL350M
OLL-0	LL-400A	LL105	OLL-0M	LL-400M	LL400M
LL COVER GASKET			LL COVER GASKET		
OLL-1CG	LL-50ACGA	LL15CGN	OLL-1MCG	-	LL50MCG
OLL-2CG	LL-75ACGA	LL25CGN	OLL-2MCG	-	LL75MCG
OLL-3CG	LL-100ACGA	LL35CGN	OLL-3MCG	-	LL100MCG
OLL-4CG	LL-125ACGA	LL45CGN	OLL-4MCG	-	LL125MCG
OLL-5CG	LL-150ACGA	LL55CGN	OLL-5MCG	-	LL150MCG
OLL-6CG	LL-200ACGA	LL65CGN	OLL-6MCG	-	LL200MCG
OLL-7CG	-	LL75CGN	OLL-7MCG	-	LL250MCG
OLL-8CG	-	LL85CGN	OLL-8MCG	-	LL300MCG
OLL-9CG	-	LL95CGN	OLL-9MCG	-	LL350MCG
OLL-0CG	-	LL105CGN	OLL-0MCG	-	LL400MCG
LR			LR		
OLR-1	LR-50A	LR15	OLR-1M	LR-50M	LR50M
OLR-2	LR-75A	LR25	OLR-2M	LR-75M	LR75M
OLR-3	LR-100A	LR35	OLR-3M	LR-100M	LR100M
OLR-4	LR-125A	LR45	OLR-4M	LR-125M	LR125M
OLR-5	LR-150A	LR55	OLR-5M	LR-150M	LR150M
OLR-6	LR-200A	LR65	OLR-6M	LR-200M	LR200M
OLR-7	LR-250A	LR75	OLR-7M	LR-250M	LR250M
OLR-8	LR-300A	LR85	OLR-8M	LR-300M	LR300M
OLR-9	LR-350A	LR95	OLR-9M	LR-350M	LR350M
OLR-0	LR-400A	LR105	OLR-0M	LR-400M	LR400M
LR COVER GASKET			LR COVER GASKET		
OLR-1CG	LR-50ACGA	LR15CGN	OLR-1MCG	-	LR50MCG
OLR-2CG	LR-75ACGA	LR25CGN	OLR-2MCG	-	LR75MCG
OLR-3CG	LR-100ACGA	LR35CGN	OLR-3MCG	-	LR100MCG
OLR-4CG	LR-125ACGA	LR45CGN	OLR-4MCG	-	LR125MCG
OLR-5CG	LR-150ACGA	LR55CGN	OLR-5MCG	-	LR150MCG
OLR-6CG	LR-200ACGA	LR65CGN	OLR-6MCG	-	LR200MCG
OLR-7CG	-	LR75CGN	OLR-7MCG	-	LR250MCG
OLR-8CG	-	LR85CGN	OLR-8MCG	-	LR300MCG
OLR-9CG	-	LR95CGN	OLR-9MCG	-	LR350MCG
OLR-0CG	-	LR105CGN	OLR-0MCG	-	LR400MCG

FITTINGS

O SERIES/Form 5



ALUMINUM			IRON		
KILLARK O SERIES	APPLETON FORM 85™ UNILETS™	CROUSE-HINDS CONDULET® SERIES 5	KILLARK DURALOY® 5	APPLETON FORM 35™	CROUSE-HINDS FORM 5
T			T		
OT-1	T-50A	T15	OT-1M	T-50M	T50M
OT-2	T-75A	T25	OT-2M	T-75M	T75M
OT-3	T-100A	T35	OT-3M	T-100M	T100M
OT-4	T-125A	T45	OT-4M	T-125M	T125M
OT-5	T-150A	T55	OT-5M	T-150M	T150M
OT-6	T-200A	T65	OT-6M	T-200M	T200M
OT-7	T-250A	T75	OT-7M	T-250M	T250M
OT-8	T-300A	T85	OT-8M	T-300M	T300M
OT-9	T-350A	T95	OT-9M	T-350M	T350M
OT-0	T-400A	T105	OT-0M	T-400M	T400M
T COVER GASKET			T COVER GASKET		
OT-1CG	T-50ACGA	T15CGN	OT-1MCG	-	T50MCG
OT-2CG	T-75ACGA	T25CGN	OT-2MCG	-	T75MCG
OT-3CG	T-100ACGA	T35CGN	OT-3MCG	-	T100MCG
OT-4CG	T-125ACGA	T45CGN	OT-4MCG	-	T125MCG
OT-5CG	T-150ACGA	T55CGN	OT-5MCG	-	T150MCG
OT-6CG	T-200ACGA	T65CGN	OT-6MCG	-	T200MCG
OT-7CG	-	T75CGN	OT-7MCG	-	T250MCG
OT-8CG	-	T85CGN	OT-8MCG	-	T300MCG
OT-9CG	-	T95CGN	OT-9MCG	-	T350MCG
OT-0CG	-	T105CGN	OT-0MCG	-	T400MCG
X			X		
OX-1	X-50A	X15	OX-1M	X-50M	X50M
OX-2	X-75A	X25	OX-2M	X-75M	X75M
OX-3	X-100A	X35	OX-3M	X-100M	X100M
OX-4	-	X45	OX-4M	X-125M	X125M
OX-5	-	X55	OX-5M	X-150M	X150M
OX-6	-	X65	OX-6M	X-200M	X200M
X COVER GASKET			X COVER GASKET		
OX-1CG	-	-	OX-1MCG	-	X50MCG
OX-2CG	-	-	OX-2MCG	-	X75MCG
OX-3CG	-	-	OX-3MCG	-	X100MCG
OX-4CG	-	-	OX-4MCG	-	X125MCG
OX-5CG	-	-	OX-5MCG	-	X150MCG
OX-6CG	-	-	OX-6MCG	-	X200MCG



KILLARK

ALUMINUM			IRON		
KILLARK O SERIES	APPLETON FORM 85™ UNILETS™	CROUSE-HINDS CONDULET® SERIES 5	KILLARK DURALOY® 5	APPLETON FORM 35™	CROUSE-HINDS FORM 5
TB			TB		
OTB-1	TB-50A	TB15	OTB-1M	TB-50M	TB50M
OTB-2	TB-75A	TB25	OTB-2M	TB-75M	TB75M
OTB-3	TB-100A	TB35	OTB-3M	TB-100M	TB100M
OTB-4	TB-125A	TB45	OTB-4M	TB-125M	TB125M
OTB-5	TB-150A	TB55	OTB-5M	TB-150M	TB150M
OTB-6	TB-200A	TB65	OTB-6M	TB-200M	TB200M
TA			TA		
OTA-1	-	-	OTA-1M	TA-50M	-
OTA-2	-	-	OTA-2M	TA-75M	-
-	-	-	OTA-3M	TA-100M	-
E			E		
OE-1	E-50A	-	OE-1M	E-50M	-
OE-2	E-75A	-	OE-2M	E-75M	-
OE-3	E-100A	-	OE-3M	E-100M	-
E COVER GASKET			E COVER GASKET		
OE-1CG	-	-	-	-	-
OE-2CG	-	-	-	-	-
OE-3CG	-	-	-	-	-