

Stainless Steel

Conduit Bodies

for Harshest Environments



CROSS REFERENCE BY MANUFACTURER

316 STAINLESS STEEL				
KILLARK	CROUSE-HINDS	CALBRITE	GIBSON	T&B
LB COVER GASKET				
LB28SS	LB28SS	S60700LB00	7075LB	LB28SST
LB38SS	LB38SS	S61000LB00	7100LB	LB38SST
LB58SS	LB58SS	S61500LB00	7150LB	LB58SST
LB68SS	LB68SS	S62000LB00	7200LB	LB68SST
C COVER GASKET				
C28SS	C28SS	S60700LR00	7075C	—
C38SS	C38SS	S61000LR00	7100C	—
C58SS	C58SS	S61500LR00	7150C	—
C68SS	C68SS	S62000LR00	7200C	—
LL COVER GASKET				
LL28SS	LL28SS	S60700LL00	7075LL	—
LL38SS	LL38SS	S61000LL00	7100LL	—
LL58SS	LL58SS	S61500LL00	7150LL	—
LL68SS	LL68SS	S62000LL00	7200LL	—

316 STAINLESS STEEL				
KILLARK	CROUSE-HINDS	CALBRITE	GIBSON	T&B
LR COVER GASKET				
LR28SS	LR28SS	S60700CE00	7075LR	—
LR38SS	LR38SS	S61000CE00	7100LR	—
LR58SS	LR58SS	S61500CE00	7150LR	—
LR68SS	LR68SS	S62000CE00	7200LR	—
T COVER GASKET				
T28SS	T28SS	S60700TE00	7075T	T28SST
T38SS	T38SS	S61000TE00	7100T	T38SST
T58SS	T58SS	S61500TE00	7150T	T58SST
T68SS	T68SS	S62000TE00	7200T	T68SST
TB COVER GASKET				
TB28SS	TB28SS	S60700TB00	7075TB	TB28SST
TB38SS	TB38SS	S61000TB00	7100TB	TB38SST
TB58SS	TB58SS	S61500TB00	7150TB	TB58SST
TB68SS	TB68SS	S62000TB00	7200TB	TB68SST



Are You Following Us?



SS_Cross Reference 08-20 © Killark, 2020

KILLARK[®]

www.hubbell.com/killark/en/



Harsh & Hazardous