



L101045G

by Wiegmann
Catalog ID: L101045G

N1 45 Degree Elbow (Hinged-Cover/Screw-Cover Wireway) 10X10 Carbon Steel - Galvanized

- Galvanized 45 degrees elbow fitting.

Product Details

General

Accessory Type	Elbow
Application	For use with HS and S Series wireway.
Cover Type	Hinged/Screw Cover
Finish Type	Galvanized
Fitting Type	45 Degree Elbow
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Type	Fitting
UPC	786725852826

Dimensions

Actual Depth	17.750 in
Actual Height	10.500 in
Actual Length	17.750 in
Actual Width	15.250 in
Depth	18 in
Height	11 in
Weight	6 lb
Width	10 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	1
UL Listed	Yes