



L121290G

by Wiegmann
Catalog ID: L121290G

N1 90 Degree Elbow (Hinged-Cover/Screw-Cover Wireway) 12X12 Carbon Steel - Galvanized

- Galvanized 90 degrees elbow fitting.

Product Details

General

Accessory Type	Elbow
Application	For use with HS and S Series wireway.
Cover Type	Hinged/Screw Cover
Finish Type	Galvanized
Fitting Type	90 Degree Elbow
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Type	Fitting
UPC	786725852772

Dimensions

Actual Depth	18.500 in
Actual Height	11.250 in
Actual Length	18.500 in
Actual Width	12.060 in
Depth	19 in
Height	11 in
Weight	19 lb
Width	12 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	1
UL Listed	Yes