



L1A1-350

by CMC
Catalog ID: L1A1-350

General purpose transformer connectors, Dual rated connectors for Aluminum or Copper conductors, CO-OX
Oxide inhibitor is omitted

- Clear Plated for low-contact resistance.
- Fully tested to ANSI C119.4 for Class ‘A’ connectors.
- Supplied with aluminum radial tipped set-screws.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Designed for installation on standard two and four-hole spades.
- All mounting holes 1.75” on center line.
- For installation, CMC® recommends the use of a 9” insulated Allen wrench.
- A torque wrench should be used to ensure the proper torque is achieved.

Product Details

General

| | |
|-------------------|-------------------------|
| Material | Aluminum Alloy, 6061-T6 |
| Number Of Outlets | 1 |
| Type | Bolted Lugs & Terminals |
| UPC | 192663074587 |

Dimensions

| | |
|--------|---------|
| Depth | 0.56 in |
| Height | 1.19 in |
| Length | 2.25 in |
| Width | 1.25 in |

Electrical Ratings

| | |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

Conductor Related

| | |
|-----------------|---------------------|
| Conductor Range | 350 Kcmil - #12 AWG |
|-----------------|---------------------|



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

