

Connector, Parallel Groove

by ANDERSON
Catalog ID: LC1155

Two U-Bolt Bronze Parallel Groove Connector



* Representative image

Product Details

General

Bolt Head Type	U-Bolt
Bolt Installation Torque (Recommended)	0 ft-lbs
Cover Available	No
Material - Body	Bronze
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Spacer	Bronze
Material - Washer	Stainless Steel
Plating	No
Product Category	Mechanical Connectors
Style	Two U-Bolt
UPC	096359319467

Dimensions

Bolt Diameter	0.500 in
Diameter - Bolt	0.5 in
Height	4.000 in
Length	3.375 in
Weight	2.352 lb
Width	2.937 in

Conductor Related

Conductor Diameter (Tap) - Maximum	0.813 in
Conductor Diameter (Tap) - Minimum	0.46 in
Conductor Type	Copper

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	480 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com