

# Connector, Parallel Groove

by ANDERSON  
Catalog ID: LC1177

Two U-Bolt Bronze Parallel Groove Connector



\* Representative image

## Product Details

### General

Bolt Head Type	U-Bolt
Bolt Installation Torque (Recommended)	0 ft-lbs
Cover Available	No
Material - Body	Bronze
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Hex Nut	Stainless Steel
Material - Keeper	Bronze
Material - Spacer	Bronze
Material - Washer	Stainless Steel
Plating	No
Product Category	Mechanical Connectors
Style	Two U-Bolt
UPC	096359319481

### Dimensions

Bolt Diameter	0.500 in
Diameter - Bolt	0.5 in
Height	5.000 in
Length	4.000 in
Weight	3.528 lb
Width	3.062 in

**Conductor Related**

Conductor Diameter (Tap) - Maximum	1.152 in
Conductor Diameter (Tap) - Minimum	0.811 in
Conductor Type	Copper

**Certifications and Compliance**

UL Listed	No
-----------	----

**For further technical assistance, please contact us****Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)