

LI350-6

by CMC

Catalog ID: LI350-6



Dual-Rated For Aluminum or Copper Conductors

- Unique lay-in feature reduces frustration of feeding multiple conductors through standard connectors
- Each outlet has a removable “keeper” that allows conductors to be laid into the outlet, solving the problem of trying to bend in confined areas. The “keeper” is then slid over the conductor and the set-screws are tightened. It is fast and easy at initial installations, and for later service additions
- Connectors are fabricated from 6061-T6 aluminum alloy and clear plated for high conductivity and strength
- Fully tested ANSI C119.4 for Class ‘A’ connectors
- CMC® recommends the use of a 9” insulated wrench for installations

Product Details

General

Material	Aluminum
UPC	192663080861

Dimensions

Height	1.75 in
Length	6.912 in
Width	1.25 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	350 Kcmil - #10 AWG
-----------------	---------------------



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

