



COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

Threaded Conduit Fittings: LL Body Only
1/2" Rigid LL Type Body

C13.1



TRADE SIZE	CATALOG NUMBER	A	B	C	D	E	F
1/2"	LL050	4.33 (109.5)	2.00 (51.5)	1.36 (34.5)	1.56 (39.5)	1.34 (34.0)	1.50 (38.0)
G TAPPED HOLES	NPT THREAD	NPT TUBING TO FITTING PLUG GAGE		THREAT DIA	VOLUME		MAXIMUM WIRE TELL
PG 50/UNC 2B	1/2-14NPT	5/16 MAX		0.611	4.3 CUB IN		
		5 MIN		1.554	79.0 CC		

Catalog #: LL050

APPLICATIONS

For use with threaded Rigid/IMC conduit, for pulling access or to split a run into multiple directions.
N/A

PRODUCT FEATURES

Durable die cast aluminum construction
Premium powder coat finish
Combination head screw

CULUS

Listed

NEMA

NEMA 3R Rated

NEC

2014 NEC Compliant

GENERAL PRODUCT INFORMATION

Trade Size: 1/2"
Description Table: 1/2" Rigid LL Type Body

PACKAGING

Package Type: Carton
Std. Pkg.: 10
Ship Carton Qty.: 100
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 20
Ship Carton Length (in.): 20.87
Ship Carton Width (in.): 11.81
Ship Carton Height (in.): 9.84
Ctn Weight (Lbs.): 25.79
Pallet Qty: 2400
UPC Number: 050169816806
I2of5: 50050169816801