

LPLE24-750SSC

by CMC
Catalog ID: LPLE24-750SSC

Pad mounted termination enclosures, Three-Phase, NEMA 3R (rain-proof), 600 Volt Rated, Includes ground straps, Stainless steel cabinets, Enclosure is made with a lift-off (removable) top

- Aluminum mechanical bar connector eliminates compression tools, lugs and bolt assemblies
- Aluminum enclosure is lightweight, low maintenance and has excellent corrosion resistance
- Ample working space, allowing for easier termination with a removable swinging door
- All-welded construction: welds and seams are ground smooth
- Manufactured to meet or exceed ANSI C57-12.28 for wall-mount equipment enclosure integrity
- Removable swinging doors - Doors have stainless steel lift off hinges with stainless steel three-point locking handles and recessed stainless steel penta-head bolts for security
- Finish is Munsell green, oven cured powder coat
- All mounting hardware is 18-8 stainless steel
- Any pad mount enclosure can be made with a lift-off (removable) top. In order to designate this use “LPLE” instead of “LPTE”



Product Details

General

| | |
|----------|--------------|
| Material | Aluminum |
| UPC | 192663112128 |

Dimensions

| | |
|--------|-------|
| Depth | 54 in |
| Height | 44 in |
| Width | 48 in |

Electrical Ratings

| | |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

Conductor Related

| | |
|----------------------|--------------------|
| Conductor Range | 750 Kcmil - #2 AWG |
| Number Of Conductors | 24 |